## **METALLURGICAL MICROSCOPES**





5102-M600

- Infinite optical system, observation in reflected or transmitted illumination, polarizing observation
- Kohler illumination system provides uniform illumination field
  Objectives 40X, 60X are spring type





blue filter (included)

frosted glass filter (included)

## **SPECIFICATION**

Code	5102-M600** (bright field objectives)				5102-M600BD** (bright & dark field objectives)			
Illumination	6V/30W (transmitted) 6V/30W (reflected)		12V/30W (transmitted)		12V/50W (reflected)			
Objective	bright field objectives				bright & dark field objectives			
(infinite plan achromatic)	5X	10X	40X	60X	5X	10X	20X	40X
Working distance	26.1mm	20.2mm	3.98mm	3.18mm	9.70mm	9.30mm	7.20mm	3.00mm
Numerical aperture	0.12	0.25	0.60	0.70	0.12	0.25	0.40	0.70
Magnification	50X~600X			50X~400X				
Eyepiece (wide field)	10X (view field: Ø22mm)							
	double layer							
Stage	size: 210×140mm							
	travel: 75x50mm							
Pupil distance	53~75mm	53~75mm						
Diopter adjustment	±5 diopter (c	±5 diopter (one eyepiece)						
Power supply	220V, 50/60Hz **							
Dimension (L×W×H)	456×260×498mm							
Weight	11kg							

<sup>\*\*</sup> Add "-U" on code No. when power supply is 110V, 50/60Hz

## STANDARD DELIVERY

VIAIDARD DELIVER		
Main unit	1 pc	
Anti-dust cover	1 pc	
Filter (blue/frosted glass)	1 pc of each	

## **OPTIONAL ACCESSORY**

0. 1.0.0.12.100200011			
	PL50X	5101-M-BD50X	
Bright & dark field objective	PL60X	5101-M-BD60X	
(for 5102-M600BD)	PL80X	5101-M-BD80X	
(*** * * * * * * * * * * * * * * * * *	PL100X	5101-M-BD100X	
10X dividing eyepiece	5101-M-EPD10X		

Bright field objective (for 5102-M600)	PL20X	5101-M-OB20X		
	PLZUA	3101-WI-OBZUA		
	PL50X	5101-M-OB50X		
	PL80X	5101-M-OB80X		
	PL100X	5101-M-OB100X		
Digital camera		ISM-CM20, ISM-CM63, ISM-ZS70-S		
Camera adapter *		5101-M-ADAPTER		

<sup>\*</sup>Digital camera must be used with camera adapter